



USB A Female to USB A Male USB 2.0 Extension Cable 480 Mbps 1m/3.3ft Black

V7USB2EXT-01M-1E

SKU: J154507

V7 High-Speed USB cables are designed to connect computer peripherals such as digital cameras, printers, scanners, personal media players, external high disk drives, flash drives and network adapters. The V7 USB Extension Cables are backward compatible with USB 1.0/1.1 devices. These fully shielded USB cables feature high-grade PVC jacket construction combined with shielded twisted pair data-lines, providing excellent performance.

- Faster charging and data communication between devices
- Simple plug-and-play connectivity
- High grade shielding resistant to EMI and RF
- Built with corrosion-resistant connectors and strain relief for optimal signal transfer, fit and durability
- Manufactured in our ISO certified facilities and backed by V7's warranty

General

Sku: J154507
Model: V7USB2EXT-01M-1E
UPC: 662919033335
Warranty: Lifetime
Compliance: CE, RoHS, WEEE
Country Of Origin: Vietnam
Package Type: Polybag

Color

Color: Black

Package Dimensions

Package Dimensions (L/W/H): 6.3 x 8.27 x 0 in (160 x 210 x 0.1 mm)
Shipping Weight: 0.04 kg (0.09 lbs)

Product Dimensions

Product Weight: 0.03 kg (0.07 lbs)

Technical

Conductor: Tin Plated Copper
Cable Length: 1m/3.3ft
Conductor Size: 28AWG
Shielding: Aluminum Mylar foil with Braid
Standard: USB 2.0
Connectors: USB
Fire Rating: VW-1
Cable diameter: 4.0mm
Connector 1: USB A Female
Connector 2: USB A Male
Number of Conductors: 4
Data Transfer Rate: 480 Mbps