

## Electrolube® GLC

### Glass Cleaner

#### DESCRIPTION

**Electrolube® GLC** is an extremely efficient, low foaming cleaner which is classified as non-flammable and non-hazardous. It is available in a 500 mL trigger spray bottle for hand applications.

READ ENTIRE TECHNICAL BULLETIN BEFORE USING THIS PRODUCT

#### FEATURES AND BENEFITS

- Water-based, non-flammable, silicone-free cleaner; ideal for all types of glass
- Removes oil, grease, and other light organic residues
- Also suitable for removing traffic film and nicotine stains
- Can be used in conjunction with our Engineering Cleaning Wipes, ECW

#### PRODUCT INFORMATION

Please contact your customer service representative for information on available package sizes.

#### PHYSICAL PROPERTIES

Category	Results
<b>Typical Properties</b>	
Form	Colorless liquid
Density (g/mL)	1.00
Boiling Point (°C)	>100
Flash Point	None

## APPLICATION GUIDELINES

To use spray the liquid liberally and wipe clean with a lint free cloth such as our Engineering Cleaning Wipes (ECW025). For heavy deposits a second application may be necessary. GLC is suitable for all industrial and domestic purposes.

## ADDITIONAL INFORMATION

**Shelf Life:** 48 Months

## SAFETY & WARNING

It is recommended that the company/operator read and review the Safety Data Sheets for the appropriate health and safety warnings before use. **Safety Data Sheets are available.**

## CONTACT INFORMATION

[www.macdermidalpha.com](http://www.macdermidalpha.com)

<b>North America</b> 140 Centennial Avenue Piscataway, NJ 08854 1.800.367.5460	<b>Europe</b> Ashby Park Coalfield Way Ashby de la Zouch Leicestershire, LE65 1JR, UK 44.01530.41960	<b>Asia</b> 8/F., Two Sky Parc 51 Hung To Road Kwun Tong, Kowloon, Hong Kong, SAR China 852.2500.5365
---	---	--

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product. READ IT THOROUGHLY PRIOR TO PRODUCT USE. Emergency safety directory assistance: US 1 202 464 2554, Europe + 44 1235 239 670, Asia + 65 3158 1074, Brazil 0800 707 7022 and 0800 172 020, Mexico 01800 002 1400 and (55) 5559 1588

**DISCLAIMER:** All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OF MERCHANTABILITY, WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory. Products are warranted to be free from defects in material and workmanship at the time sold. The sole obligation of seller and manufacturer under this warranty shall be to replace any noncompliant product at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct, indirect, incidental or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are supplied in response to a customer request that specifies operating parameters beyond those stated above, or if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect, incidental and consequential damages that may result from use of the products under such conditions, and agrees to exonerate, indemnify, defend and hold harmless MacDermid, Incorporated and its affiliates therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in a manner that infringes any patent or other intellectual property rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

© 2019 MacDermid, Inc. and its group of companies. All rights reserved. "(R)" and "TM" are registered trademarks or trademarks of MacDermid, Inc. and its group of companies in the United States and/or other countries.