

LED lamp 025 Magnetic fixing 24-48 V DC



Model			
product brand name	SIVACON		
product designation	LED light		
design of the product	Without screw fixing		
type of light source	LED not replaceable		
General technical data			
consumed active power of the light source	5 W		
type of voltage of the operating voltage	DC		
Protection class			
protection class IP	IP20		
Product details			
product component			
• ON/OFF switch			
• light sensor			
• socket outlet			
product feature magnetic	Yes		
Connections			
type of electrical connection for through-wiring	Plug-in connection		
Mechanical Design			
height	34 mm		
width	32 mm		
depth	34 mm		
length	351 mm		
fastening method	magnetic fixing		
net weight	0.2 kg		
material	plastic		
Approvals Certificates			
General Product Approval	other	Dangerous goods	Environment



[Confirmation](#)

[Transport Information](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2201-1A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2201-1A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2201-1A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/24/2025 

