


E40473



Welding adapters EN10357 series A

ADAPT EN10357 DN50



Application	
Design	for volumetric flow meters SMF
Application	food and beverage industry; hygienic systems
Pressure rating	25 bar 2.5 MPa
Tests / approvals	
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.
Mechanical data	
Weight [g]	2567.9
Materials	stainless steel (316L/1.4404)
Nominal diameter	DN50 (2")
Sensor connection	ifm-specific device flange
Process connection	welding adapter EN10357 series A (DIN)
Process connection suitable for pipe standard	(DIN EN 10357 series A); (DIN 11866 series A); (DIN 11850 series 1); (DIN 11850 series 2)
Surface characteristics Ra/Rz of the wetted parts	$Ra \leq 0.4 \mu m$

E40473



Welding adapters EN10357 series A

ADAPT EN10357 DN50

Accessories	
Items supplied	screws 8
Remarks	
Pack quantity	2 pcs.