

### S766 - Hi-Vis 5-in-1 Contrast Essential Jacket

**Collection:** 300D Industry High Visibility

**Range:** High Visibility

**Shell Fabric:** 300D Industry: 100% Polyester, 300D Oxford, Stain Resistant Finish, Double PU Coated, 190g

**Outer Carton:** 12

#### Product information

An adaptable, functional style offering excellent value for money. Outer jacket contains two useful large patch pockets with stud adjustable cuffs and a concealed adjustable hood, whilst the inner waterproof jacket has detachable fluorescent fleece sleeves, 2 spacious side pockets and has dark contrast panels for protection against dirt.

#### 300D Industry High Visibility

A comprehensive range of single and combination garments in a highly durable, EN343 certified fabric including some new cleverly designed and innovative styles.

#### High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

#### Standards

EN ISO 20471 Class 3  
RIS 3279 TOM Issue 2 (Orange Only)  
EN 343 Class 3:1 X (WP 15,000mm)  
EN 342 (0.352 (M<sup>2</sup>.K/W), 2, X)  
AS 4602.1:2024 Class D/N



#### Features

- Waterproof with taped seams preventing water penetration
- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- EN342 Protection against cold certified up to -36°C
- Stud adjustable cuffs for a secure fit
- Two lower pockets
- Inner chest pocket
- Contrast panels for protection against dirt
- Jacket can be worn five ways for multi use
- Reflective tape for increased visibility
- Detachable inner jacket for added versatility in all weather conditions
- Detachable sleeves provides a multi-way option for wearer

**S766 - Hi-Vis 5-in-1 Contrast Essential Jacket**  
**Commodity Code: 6210200010**

**Test House**

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
 Bracetown Business Park  
 D15 YN2P, Ireland  
 Cert No: 2777/13391-04/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)  
 SATRA Technology Park  
 NN16 8SD, United Kingdom  
 Cert No: AB0321/17283-01/E00-00

**Wash Care**



**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
S766YBRS	Yellow/Black	65.0	45.0	47.0	1.7070	0.1375	5036108340903	25036108829617
S766YBRM	Yellow/Black	65.0	45.0	47.0	1.7490	0.1375	5036108340897	25036108829600
S766YBRL	Yellow/Black	65.0	45.0	47.0	1.8380	0.1375	5036108340880	25036108829594
S766YBRXL	Yellow/Black	65.0	45.0	47.0	1.9200	0.1375	5036108340910	25036108829624
S766YBRXXL	Yellow/Black	65.0	45.0	47.0	2.0300	0.1375	5036108340927	25036108829631
S766YBRXXXL	Yellow/Black	65.0	45.0	47.0	2.0500	0.1375	5036108340934	25036108829648
S766YBR4XL	Yellow/Black	65.0	45.0	47.0	1.9500	0.1375	5036108349593	25036108838213
S766YBR5XL	Yellow/Black	65.0	45.0	47.0	1.9500	0.1375	5036108349609	25036108838220