

# Actuator

46-

2131.1120.000

Distribution by  
Rs-online<https://www.rs-online.eao.com/component/46-21...>

Your product:

---



## 46-2131.1120.000 Actuator

*Loading ...*

### FRONT

|                       |         |
|-----------------------|---------|
| Front dimension:      | Ø 29 mm |
| Front form:           | Round   |
| Front bezel colour:   | Black   |
| Front bezel material: | Plastic |

### MOUNTING

|                   |                |
|-------------------|----------------|
| Design:           | Raised         |
| Mounting cut-out: | Ø 22.3 mm      |
| Mounting type:    | Panel mounting |

### OPERATING-/INDICATION PART

|                    |                        |
|--------------------|------------------------|
| Lens colour:       | Red                    |
| Lens material:     | Plastic                |
| Lens illumination: | Non illuminated        |
| Lens shape:        | Flush                  |
| Lens optics:       | opaque                 |
| Lens type:         | Level with front bezel |

### ELECTRICAL CHARACTERISTICS

|                   |                                 |
|-------------------|---------------------------------|
| Pollution degree: | 3                               |
| Protection class: | II, according to EN / IEC 61140 |

## MECHANICAL CHARACTERISTICS

|                             |                                  |
|-----------------------------|----------------------------------|
| <b>Switching action:</b>    | Momentary                        |
| <b>Mechanical lifetime:</b> | 1 Mil. cycles of operation       |
| <b>Tightening torque:</b>   | 2 ... 3 Nm (17.7 ... 26.6 Lb-in) |
| <b>Weight:</b>              | 0.022 kg                         |

## AMBIENT CONDITION


|                               |                                                                |
|-------------------------------|----------------------------------------------------------------|
| <b>IP front protection:</b>   | IP65                                                           |
| <b>IK front protection:</b>   | IK03                                                           |
| <b>Operating temperature:</b> | – 25 °C ... + 55 °C                                            |
| <b>Shock resistance:</b>      | 30g, 18ms (EN-IEC 60068-2-27)<br>50g, 11ms (EN-IEC 60068-2-27) |
| <b>Vibration resistance:</b>  | 5g f= 2...500Hz (EN-IEC 60068-2-6)                             |
| <b>Climate resistance:</b>    | +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)                   |

## CERTIFICATE

|                      |                                                    |
|----------------------|----------------------------------------------------|
| <b>Approbations:</b> | CSA, EAC, UL                                       |
| <b>Conformities:</b> | CE                                                 |
| <b>REACH:</b>        | REACH compliant                                    |
| <b>RoHS:</b>         | RoHS compliant                                     |
| <b>Standards:</b>    | CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508 |

## OTHER

|                                           |                                                                                                                          |
|-------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|
| <b>Short Description:</b>                 | Actuator, Ø 22.3 mm, Ø 29 mm, Flush, Non illuminated, Red, Plastic, opaque, Round, Black, Plastic, Momentary, IP65, IK03 |
| <b>Housing colour:</b>                    | Black                                                                                                                    |
| <b>Housing material:</b>                  | Plastic                                                                                                                  |
| <b>max. number of switching elements:</b> | 8                                                                                                                        |
| <b>Mounting cut-outs:</b>                 |                                                                                                                          |



**Dimension drawings:**

