
KEMET Part Number: SSHB21H-R25056

(UALSB2R2505600)



KEMET, SSHB21H, AC Line Filters, Dual Mode, 5600 uH



Dimensions		
L	26mm MAX	
Т	23mm MAX	
Н	15.5mm MAX	
LL	3.5mm +/-0.5mm	
S	21mm +/-0.5mm	

Packaging Specifications		
Packaging:	Tray	
Packaging Quantity:	360	
Weight:	14 g	

General Information		
Series:	SSHB21H	
Style:	Through-Hole	
RoHS:	Yes	
Notes:	Marking: R25 Lot No.	
Miscellaneous:	Temperature Rise Maximum: 60 K	

Specifications		
Voltage AC:	250 VAC	
Inductance:	5.6 mH (10 kHz)	
Current:	2.5 A	
Temperature Range:	-25/+120°C	
DC Resistance:	100 mOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

