



Kombinationstabelle
Combination table
Tableau des combinaisons
 Ver. 04.10.2023

Valve Manufacturer	Ventiltyp Valve type Type de vanne	DN min / max	Max. Temperatur Max. temperature Max. température	AVM105(S)...	AVM115(S)F...	AVM115SA	AVF124(S)F...	AVF125(S)F...	AVM2155F123R AVM215F120R	AVM322(S)...	AVM327(S)...	AVM2345F132 AVF2345F132 AVN2345F132
Belimo	H6..R	15...65								0510390 027	0510390 012	
Belimo	H7..R	15...65								0510390 027	0510390 012	
Belimo	H4..B	15...50								0510390 027	0510390 012	
Belimo	H5..B	15...50								0510390 027	0510390 012	
Belimo	H6..N	15...65								0510390 027	0510390 012	
Belimo	H7..N	15...65								0510390 027	0510390 012	
Danfoss	VRB - VRG	15..50							0510390040			
Danfoss	VFS / VL / VF	15...50							0510390039			
Danfoss	VEFS2	25..50							0510390039			
Frese	OPTIMA Compac Threaded	40...50							0510390029	0510390041		
Frese	OPTIMA Compac Flange	50...80							0510390038	0510390028		
Frese	OPTIMA Compac Flange	100...300										0510390053
Herz	RBV	80-100										0510390057
Herz	TV/PV	32-50										0510390057
Herz	KV/KVP	65-80										0510390056
Herz	PV/TV	15-25							0510390055			
Herz	KV/KVP	15-50							0510390055			
Herz	RBV	50-65							0510390055			
Honeywell	V5013R	15 ... 50	120°C							0510390024	0510390008	
Honeywell	V5016A	15 ... 80	130°C						0510390024	0510390008	0372378001	
Honeywell	V5025A	15 ... 80	130°C						0510390024	0510390008	0372378001	
Honeywell	V5049A	15 ... 65	130°C						0510390024	0510390008	0372378001	
Honeywell	V5049B	15 ... 65	130°C						0510390024	0510390008	0372378001	
Honeywell	V5050A	15 ... 80	130°C						0510390024	0510390008	0372378001	
Honeywell	V5095A	15 ... 80	130°C						0510390024	0510390008	0372378001	
Honeywell	V5328A	15 ... 80	130°C						0510390024	0510390008	0372378001	
Honeywell	V5329A	15 ... 80	130°C						0510390024	0510390008	0372378001	
Honeywell	V5049A	80 ... 150	130°C									0372378002
Honeywell	V5049B	80 ... 150	130°C									0372378002
Honeywell	V5025A	100 ... 150	130°C									0372378002
Honeywell	V5050A	100 ... 150	130°C									0372378002
IMI	KTM512	65-100							0510390037			
IMI	KTM512	15-50							0510390036			
IMI	CV	15-50							0510390035			
IMI	TA-Fusion	32...50							0510390033			
IMI	TA-Fusion	65...80							0510390034			
ITT-Dräger	PSVF	15 ... 32	130°C							0510390 026	0510390010	0372389001
ITT-Dräger	PSVD	15 ... 32	130°C							0510390 026	0510390010	0372389001
ITT-Dräger	SVF	15 ... 32	130°C							0510390 026	0510390010	0372389001
ITT-Dräger	SVD	15 ... 32	130°C							0510390 026	0510390010	0372389001
ITT-Dräger	PSVF	40 ... 50	130°C									0372389002
ITT-Dräger	PSVD	40 ... 50	130°C									0372389002
ITT-Dräger	SVF	40 ... 50	130°C									0372389002
ITT-Dräger	SVD	40 ... 50	130°C									0372389002
Johnson Controls	VB7216	15..50	150°C									0372377 001
Johnson Controls	VB7816	15...50	150°C									0372377 001
Johnson Controls	VBD-4xx4	15...40	150°C						0510390 023	0510390 007		0372377 001
Johnson Controls	VBD-4xx4	50...150	150°C									0372377 001
Johnson Controls	VBD-4xx8	15...40	150°C						0510390 023	0510390 007		0372377 001
Johnson Controls	VBD-4xx8	50...150	150°C									0372377 001
Johnson Controls	VBF-0xx4	15...150	150°C									0372377 001
Johnson Controls	VBF-0xx8	15...150	150°C									0372377 001
Johnson Controls	VBF-2xx4	15...40	150°C						0510390 023	0510390 007		0372377 001
Johnson Controls	VBF-2xx4	50...100	150°C									0372377 001
Johnson Controls	VBF-2xx8	15...40	150°C						0510390 023	0510390 007		0372377 001
Johnson Controls	VBF-2xx8	50...100	150°C									0372377 001
Johnson Controls	VBB-2xxx	15...100	150°C									0372377 001
Johnson Controls	VG720x	15...50	150°C									0372377 001
Johnson Controls	VG740x	15...50	150°C									0372377 001
Johnson Controls	VG780x	15...50	150°C									0372377 001
Johnson Controls	VG8..	15...50	150°C									0372377 001
Johnson Controls	VG82.. / VG84..	15...40	150°C						0510390 023	0510390 007		0372377 001
Johnson Controls	VG82.. / VG84..	50...150	150°C									0372377 001
Johnson Controls	VG8300N / H	40...150	150°C									0372377 001
Johnson Controls	VG88.. / VG89..	15...40	150°C						0510390 023	0510390 007		0372377 001
Johnson Controls	VG88.. / VG89..	50...150	150°C									0372377 001
Johnson Controls	VG94.. / VG98..	15...100	150°C									0372377 001
LDM	RV113 R	15...50	130°C							0510390 025	0510390 009	0372386 001
LDM	RV113 M	15...50	130°C							0510390 025	0510390 009	0372386 001
Satchwell	VZF1727	65 ... 100	130°C									0372387001

Kombinationstabelle
Combination table
Tableau des combinaisons
 Ver. 04.10.2023



Valve Manufacturer	Valvitypp Valve type Type de vanne	DN min / max	Max. Temperatur Max. temperature Max. température	AVM105(S)...	AVM115(S)F...	AVM115SA	AVF124(S)F...	AVF125(S)F...	AVM2155F123R AVM215F120R	AVM322(S)...	AVM327(S)...	AVM2345F132 AVF2345F132 AVN2245F132
Sauter	VDL	40 ... 50							0510390029			
Sauter	V6R / B6R	15 ... 50							0510390032		0510240012	0372338001
Sauter	V6F / B6F	15 ... 50									0510240012	0372338001
Sauter	V6G / B6G	15 ... 50									0510240012	0372338001
Sauter	V6S / B6S	15 ... 50									0510240012	0372338001
Sauter	VXD / BXD	15 ... 50									0510240012	0372338001
Sauter	VXE / BXE	15 ... 50									0510240012	0372338001
Sauter	V6F / B6F	65 ... 150										0372338002
Sauter	V6G / B6G	65 ... 150										0372338002
Sauter	V6S / B6S	65 ... 150										0372338002
Sauter	VXD / BXD	65 ... 80										0372338002
Sauter	VXE / BXE	65 ... 100										0372338002
Sauter	VQD / BQD	65 ... 80								0510390020		
Sauter	VQE / BQE	65 ... 80								0510390020		
Sauter	VUG / BUG	15 ... 50								0510390020		
Sauter	VUS / BUS	15 ... 50								0510390020		
Sauter	V66N	15 ... 50								0510390020		
Sauter	V6R / B6R	15 ... 50								0510390021		
Sauter	V6F / B6F	15 ... 50								0510390021		
Sauter	V6G / B6G	15 ... 50								0510390021		
Sauter	V6S / B6S	15 ... 50								0510390021		
Sauter	VXD / BXD	15 ... 50								0510390021		
Sauter	VXE / BXE	15 ... 50								0510390021		
Sauter	VUN / BUN	15 ... 50							0510390030			
Sauter	VUD / BUD	15 ... 50							0510390030			
Sauter	VUE / BUE	15 ... 50							0510390030			
Sauter	VQD / BQD	65 ... 80							0510390031			
Sauter	VQE / BQE	65 ... 80							0510390031			
Sauter	VUG / BUG	15 ... 50							0510390031			
Sauter	VUS / BUS	15 ... 50							0510390031			
Sauter	V66N	15 ... 50							0510390031			
Schneider	V241/V341	15-50							0510390060	0510390061	0510390061	0510390062
Schneider	V321	65-100										0510390063
Siemens	VVF21	25...80	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF21	100	130°C									0372376 014
Siemens	VXF21	25...80	130°C							0510390 022	0510390 006	0372376 010
Siemens	VXF21	100	130°C									0372376 014
Siemens	VVF31	15...80	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF31	100...150	130°C									0372376 014
Siemens	VXF31	15...80	130°C							0510390 022	0510390 006	0372376 010
Siemens	VXF31	100...150	130°C									0372376 014
Siemens	VVF40	15...80	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF40	100...150	130°C									0372376 014
Siemens	VXF40	15...80	130°C							0510390 022	0510390 006	0372376 010
Siemens	VXF40	100...150	130°C									0372376 014
Siemens	VVF41	50	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF41	65...150	130°C									0372376 014
Siemens	VXF41	15...50	130°C							0510390 022	0510390 006	0372376 010
Siemens	VXF41	65...150	130°C									0372376 014
Siemens	VVF45	50	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF45	65...150	130°C									0372376 014
Siemens	VVF52	15...40	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF52G	15...40	130°C							0510390 022	0510390 006	
Siemens	VVF52J	15...40	130°C							0510390 022	0510390 006	
Siemens	VVF52GJ	15...40	130°C							0510390 022	0510390 006	
Siemens	VVF61	15...50	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVG41	15...50	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVF52 (E / F)	15...40	130°C							0510390 022	0510390 006	0372376 010
Siemens	VVG44 / VVG44	15...50	130°C	0372273 001	0372273 001							
Siemens	VVG48 / VVG48	15...50	130°C	0372273 001	0372273 001							
Siemens	VVF/VXF 61.65...61.92	65...150	130°C									0372376 014
Siemens	VXF32 PN10	100...150	130°C									0372376015
Siemens	VXF22 PN6	100	130°C									0372376015