



PRODUCT-DETAILS

SPUL20/50M

20MM GS-PVC COAT CONDUIT 50M - GR



General Information

Extended Product Type:	SPUL20/50M
Product ID:	7TCA296030R0367
EAN:	5020963003851
Catalog Description:	20MM GS-PVC COAT CONDUIT 50M - GR
Long Description:	Liquid Tight, Medium Flexibility, Covered Steel Conduit, 1/2 Inch, Nominal Conduit Size 20mm, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 50 Meters, UL Listed and CSA Approved, PVC Covered Galvanised Steel Core with Copper Packing, Grey
Display Name:	SPUL20/50M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Flexible Protection Systems

Ordering

EAN: 5020963003851

UPC: 786210247564

Dimensions

Outside Diameter: 21.1 mm

Technical

Number of Batteries: 0

Color: Gray

Material: Galvanized Steel Core with PVC Cover and Copper Packing

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963003851

Package Level 1 Height: 9.37 in
238 mm

Package Level 1 Depth / Length: 19.25 in
489 mm

Package Level 1 Width: 19.25 in
489 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

