

Bourdon tube pressure gauges, liquid filling,

Modelcode type: 213.53.100

Item number: 82147554

Description

Design	EN 837-1
Nominal size	100 mm
Accuracy class	class 1.0
Scale range	0...40 MPa
Unit of outer Scale	MPa
Process connection	G 1/2 B
Connector location	lower mount

Materials

Measuring system	copper alloy
Movement	Copper alloy
Dial	Aluminum, white
Pointer	standard pointer
Window	polycarbonate
Bezel ring	roll formed, stainless steel
Case filling fluid	glycerine

Operating conditions

Permissible ambient temperature	-20 ... +60 °C
Ingress protection	IP 65

Options

Mounting flange/bracket	surface mounting flange, stainless steel
-------------------------	--

Labelcode

Label	WIKA standard without / with Tag-number
language of the label	German