

Han 6HPR-Compact-CM-for SCL



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 506 5411
Specification	Han 6HPR-Compact-CM-for SCL
HARTING eCatalogue	https://harting.com/09405065411

Identification

Category	Accessories
Series of hoods/housings	Han [®] HPR Compact
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings

Version

Size	6 HPR
Locking type	Screw locking

Technical characteristics

Tightening torque	3 Nm
Tightening torque (screw locking)	4 Nm
Wrench size	5
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP6K9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	130 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140192089
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467