







PCB LAYOUT (CONNECTOR REAR VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS




PANEL CUT OUT

RJXS8FP25VPE

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)

GENDER
THERMOPLASTIC 3.8mm to 5.0mm WITH CAP
TRANSMISSION CLASS (CAT5e)
VERTICAL MOUNT (PCB THRU HOLE)
POTTED
WITH EMI/RFI SHIELD



3.8-5.0mm RECOMMEND
PANEL THICKNESS

RECOMMEND MINIMUM MOUNTING PITCH



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:	
LINEAR	ANGULAR
X .X ±10	X" ±1
X.X ±5	X"X" ±30'
X.XX ±1	X"XX" ±15'
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS	
DO NOT SCALE	
DIMENSIONS IN MILLIMETRES	

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER		
MATERIAL: SEE COMPONENTS	DRN: J.W	DATE: 30/12/2024
FINISH: SEE COMPONENTS	CKD: P.M.	DATE: 30/12/2024
SCALE: NTS	APP'D: P.M.	DATE: 30/12/2024
SIZE: A3	THIRD ANGLE PROJECTION	

Amphenol		Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
TITLE: XLRnet, VERT, IP65, POTTED, SHIELDED, W/CAP, PANEL THICKNESS 3.8-5.0		PART No: RJXS8FP25VPE	REV 1
DRAWING No. 55011544-000-1		SHEET 2/2	