




Part Number : [547220504](#)
Product Description : 0.50mm Pitch SlimStack
Receptacle, Surface Mount, Dual Row,
Vertical, 1.50mm Stacking Height, Lower
Circuit Size Version, 50 Circuits, Gold Plating
with Nickel Barrier Plating Between Contact
and Tail
Series Number : 54722
Status : Active
Product Category : Board-to-Board
Connectors



Documents & Resources

Drawings
[547220504_sd.pdf](#)
[SPK-54722-001-002.pdf](#)

3D Models and Design Files
[547220504.dxf](#)
[547220504.pdf](#)
[547220504_stp.zip](#)

Specifications
[547220000-A00.pdf](#)
[PS-54722-010-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	54722
Description	0.50mm Pitch SlimStack Receptacle, Surface Mount, Dual Row, Vertical, 1.50mm Stacking Height, Lower Circuit Size Version, 50 Circuits, Gold Plating with Nickel Barrier Plating Between Contact and Tail
Series Name	0.5, BB H1.5
Application	Board-to-Board, Signal
Comments	Embossed Tape Reel Height: 380.00mm; Gold plating with Nickel plating between contact and tail
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	756054574379

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Lock to Mating Part	None
Mated Height	1.50mm
Mated Width	6.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	149.401/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	0.50mm
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Vertical SlimStack Plugs	<u>55560</u>