

Impact Driver LXT®

DTP141

18V • 1/4" • 150 Nm • 0 – 2 700 min⁻¹

Multipurpose 4-mode impact driver with three power settings

A 4-mode impact driver with an electronic torque control and four functions. The functions are impact driver, percussion drill, two-speed drill and screwdriver.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 1300 / 2200 / 2700 min ⁻¹
No load speed screwdriver	0 - 300 / 0 - 1100 min ⁻¹
Max. fastening torque Hard/Soft	22 / 13 Nm
Max Fastening Torque Impact Drill	150 Nm
Impacts per Minute (IPM)	0 - 1200 / 2400 / 3200 min ⁻¹
Percussion-drill mode	0 - 8400 / 32400 min ⁻¹
Tightening Capacity Standard Bolt	M5 - M14
Torque setting	9
Driving Shank	1/4 "
Max. Drilling Diameter in Wood	21 mm
Max. Drilling Diameter in Concrete	8 mm

User benefits

- Low power consumption thanks to brushless motor
- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- Quick mount for 1/4 "screwdriver
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

■ Optional AC

194250-8

Adaptor Chuck - 1/4 Hex Keyless



821550-0

Makpac case (2)



837670-0

MakPac (2) Inlay



■ Other

User manual

Parts drawing