




## TECH TOTAL - FLEX S3

Réf. : 70109












<b>Suitable for :</b>	Inside/Outside
<b>Type :</b>	Ankle shoe
<b>Activity :</b>	Construction / Manufacturing and assembly / Electronic Industry, ESD
<b>Upper :</b>	ON MICRO TD® microfiber, water resistant, Richelieu assembly without lateral stitching
<b>Lining :</b>	AIR SYSTEM® black color, up to the toes, slipper feeling
<b>Tongue :</b>	Bellows tongue in ON STEAM® microfiber, lined AIR SYSTEM® and padded with 10mm thick foam
<b>Ankle protection :</b>	ON STEAM® microfiber, lined AIR SYSTEM® and padded with 10mm thick foam
<b>Fastening :</b>	Eyelets and round polyester black laces
<b>Toe cap :</b>	Ultralight and extra wide 200 joules, Composite LIGHT SYSTEM®
<b>Midsole :</b>	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
<b>Insole :</b>	Thermoformed in active carbon dual density foam, antistatic, ESD and antibacterial FRESH TECH®
<b>Sole :</b>	PU 2D, TECH SOLE® ankle anti-twist system, oil resistant FO, antistatic, HI-CI
<b>Sole pattern :</b>	Multi-purpose cleated indoor/outdoor outsole, well-defined heel, cleated arch, SRC standard
<b>Weight (Kg/pair) :</b>	1.200
<b>Colors :</b>	Black upper and dark grey/black sole
<b>Sizes :</b>	35-49 (2-14)
<b>Standard :</b>	EN ISO 20345:2011 SRC / EN 61340-4-3 / DGVU 112-191
<b>CE certificate of conformity N° :</b>	0075/020/161/04/18/0585
<b>Special features :</b>	Microfiber resistant to acids and to iron or aluminium metal splashes (UNE EN ISO 20349/2011)
<b>Special features 2 :</b>	Reflective piping on the heel part
<b>Special features 3 :</b>	Wide choice of sizes: from 35 to 49!

### SPECIAL FEATURES

-  Integral 100% composite (Air System + Light System + Flex System)
-  Water absorption and penetration resistance of upper (WRU)
-  Electro Static Discharge Standard EN 61340-5-1



### GENERAL FEATURES

-  Antistatic properties (A)
-  Heel energy absorption (E)
-  Abrasion resistance
-  Crampon sole
-  Heat-insulated sole (HI)
-  Cold-insulated sole (CI)
-  200 joule extra-wide toecap
-  Hyper-ventilated lining
-  Perforation-resistance 1100 N (P)