

# Endress+Hauser Pressure sensor PMC11-AA1U1HBWBJJ

Compact gauge pressure transducer with capacitive, oil-free ceramic sensor.



Picture for reference only. Product appearance may vary based on configuration

The Cerabar PMC11 is a very compact pressure transmitter with capacitive, oil-free ceramic sensor that can measure gauge pressure from 400mbar up to 40bar ( depending on configuration) in gases, vapors, liquids and dust. The PMC11 is designed for standard applications in the process industry.

- Easy usability
- High performance
- Long term stability
- High material quality

## Configuration of PMC11-AA1U1HBWBJJ:

Approval:	AA	Non-hazardous area
Output:	1	4-20mA
Electrical Connection:	U	Valve plug ISO4400 M16, IP65 NEMA Type 4X Encl.
Sensor Range:	1H	1bar/100kPa/15psi gauge, overload: 10bar/1MPa/150psi
Calibration; Unit:	B	Sensor range; mbar/bar
Process Connection:	WBJ	Thread ISO228 G1/2 EN837, 316L
Seal:	J	EPDM

Alternative part number: PMC11-1A45/0