

D 19 VMU-10

Socket set 1/2"

28 pieces

Code
2682877

ETIM
EC002209

EAN
4010886934777

UNSPSC
27-11-17-03

Country of origin
Germany

eCl@ss
21-04-02-05

Customs tariff number
82042000



12,5 1/2" mm

Article description

- With forged, tempered hexagon (No. 19) or bi-hexagon (No. D 19) UD profile sockets, hand-operated
- With accessories made from vanadium steel 31CrV3
- With robust lever-change reversible ratchet, with push-button release
- In GEDORE blue sheet steel case
- Dimensions: 425 x 277 x 55 mm

Article parts list

Ratchet, 1993 U-10 T, Inserts, D 19 10 11 12 13 14 15 16, 17 18 19 20 21 22 23 24, 26 27 28 30 32 33 34 36, Accessories, Cross handle with sliding block 1987, Extension 1990-5-10, Cardan joint 1995

Article information

Contents (Qty of pieces)	28	Total height [mm]	55 mm
Net weight [kg]	6,7 kg	Total depth [mm]	277 mm
Total length [mm]	277 mm	Drive connector square (male)	1/2"
Total width [mm]	425 mm	Drive connector square (male)	12,7 mm