

SBO-02F12-SM





## Ordering information

Туре	Part no.
SB0-02F12-SM	6029306

Other models and accessories → www.sick.com/

## Detailed technical data


## Technical specifications

Accessory group	Distributors
Accessory family	T-junctions
Connection type head A	Female connector, M12, 8-pin, A-coded
Connection type head B	Female connector, M12, 8-pin, A-coded
Reference voltage	≤ 30 V DC
Current loading	4 A
Note	Male connector M12, 8-pin, straight, to 1 x female connector M12, 8-pin, straight and 1 x female connector M12, 8-pin, straight
Enclosure rating	IP67 <sup>1)</sup>
Ambient operating temperature	
Head	-30 °C +90 °C


 $<sup>^{1)}</sup>$  Only in fully locked position with its plugs.

## Dimensional drawing (Dimensions in mm (inch))

#### SBO-02F12-SM




## Connection type



- ① MLG sender
- ② MLG receiver
- ③ Connection cable
- MLG connection
- ⑤ T-piece
- 6 Supply Q1

#### Anschlussschema



# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

