

Features

- Tyred wheel
- Shock absorbing
- 260mm diameter
- 20mm Steel hub
- 200kg maximum load

RS PRO Pneumatic Trolley Wheel 260mm

RS Stock No.: 858-900



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A heavy-duty 260mm Pneumatic Wheel ideal for difficult surfaces including grass and gravel with a load capacity of up to 200kg.

General Specifications

Tyre Type	Pneumatic
Wheel Diameter	260mm
Bore Diameter	20mm
Bore Length	75mm
Load Capacity	200kg
Tyre Material	Rubber
Hub Material	Pressed Zincate Steel
Hub Type	Roller Bearing
Hub Diameter	20mm
Shock Absorbing	Yes