



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product compatibility	XCMD XCKD XCKT XCKP
Associated body	ZCMD29L2 ZCP39 ZCMD25L1 ZCMD21C12 ZCMD25L5 ZCT26N12 ZCMD37L1 ZCT21N12 ZCP25 ZCD26 ZCT28P16 ZCP35 ZCD39 ZCMD39L2 ZCD25 ZCMD21L1 ZCT21P16 ZCD29M12 ZCP28 ZCMD21L5 ZCP27 ZCMD69C12 ZCT26G11 ZCD21M12 ZCT26P16 ZCT21G11 ZCMD21L08U78 ZCD21

ZCMD81L1
 ZCP29M12
 ZCMD29L1
 ZCMD61C12
 ZCMD41L2
 ZCD37
 ZCMD37L2
 ZCT25G11
 ZCD28
 ZCMD41L1
 ZCT28N12
 ZCP31
 ZCMD21M12
 ZCP21
 ZCT27N12
 ZCMD39L5
 ZCMD21L08R12
 ZCMD81L5
 ZCMD61M12
 ZCT28G11
 ZCT25P16
 ZCP37
 ZCMD37L5
 ZCMD25L2
 ZCD31
 ZCMD41L5
 ZCP26
 ZCMD39L1
 ZCP29
 ZCMD81L2
 ZCMD29C12
 ZCT27G11
 ZCMD21L2
 ZCD27
 ZCT25N12
 ZCP21M12
 ZCMD29L5
 ZCD35
 ZCT27P16
 ZCD29

Movement of operating head	Multi-directional
Type of operator	Spring rod spring return metal (with silicone boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------