



MARQUARDT

SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

	ON/OFF switch (SPST)															
	1800.0102	1800.0108	1800.1102	1800.1104	1800.1108	1801.1121	1801.1148	1801.1520	1801.1908	1801.5122	1801.5524	1801.6122	1801.6123	1801.6130	1802.1425	1801.1101
single-pole																
Voltage lamp in V	230	230	230	230	230											
Actuator color / printing																
Housing color																
12 (4) A 250 V AC 1E4						•	•	•	•	•	•	•	•	•	•	•
10 (4) A 250 V AC 1E4	•	•	•	•	•											•
8 (8) A 250 V AC 5E4						•	•	•	•	•	•	•	•	•	•	
6 (4) A 250 V AC 5E4	•	•	•	•	•											•
6 (2) A 250 V AC 1E4																
4 (3) A 250 V AC 6E3																
4 (2) A 250 V AC 1E4																
30 mA 12 V 5E4																
30 mA 12 V DC 5E4																
15 A 250 V AC 1 1/2 HP						•	•	•	•	•	•	•	•	•	•	•
15 A 125 V AC 3/4 HP						•	•	•	•	•	•	•	•	•	•	•
10 A 250 V AC 1/2 HP																
10 A 125 V AC 1/3 HP																
6 A 250 V AC 1/2 HP	•	•	•	•	•											•
6 A 125 V AC 1/4 HP																•
6 A 125 - 250 V AC 1/8 HP																
6 A 125 V AC 1/10 HP																
4 A 250 V AC 1/10 HP																
Connection type																
Connection description			4.8	4.8	4.8	4.8	4.8	4.8	4.8		6.5 long				4.8	4.8
Inrush current in A (capacitive)						70	70	70	70	50	70	70	70	70	70	50
Contact distance in mm	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3
Contact material	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag
EN 60335 cap. 30 conform *G*												•			•	
Miscellaneous	sealing plate	sealing plate						snap-on rocker							two-pole housing form	
Stock version	•	•	•	•	•	•	•	•	•			•		•		•