



Outlet filter, Extract: W: 177 mm, H: 177 mm, RAL 7035, IP54,

Model		
product brand name		SIVACON
product designation		outlet filter
type of ventilation		ventilation
fan design withdrawable fan		No
design of the product EMC version		No
General technical data		
cutout width		177 mm
cutout height		177 mm
Protection class		
protection class IP		IP54
Appearance		
color		light grey
Product details		
product component fan		No
Mechanical Design		
height		204 mm
width		204 mm
depth		32 mm
installation location		Control cabinet...panels, door
fastening method		snap-on mounting
fastening method		
• 19-inch installation		No
• wall mounting		Yes
net weight		0.3 kg
material		plastic
ambient temperature during operation		
• minimum		-20 °C
• maximum		65 °C
Approvals Certificates		
General Product Approval		other
		Environment



[Confirmation](#)

[Miscellaneous](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6400-5GV30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6400-5GV30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6400-5GV30

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

