



Part Number : [194290014](#)

Product Description : MX150L 10 Circuit Panel Mount Plug for 22-14 AWG Wire, Rear Mount Flange Assembly, without Gasket, Black

Series Number : 19429

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[194290014 sd.pdf](#)

[PK-19429-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19417-001-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Connector Housings |
| Series | 19429 |
| Description | MX150L 10 Circuit Panel Mount Plug for 22-14 AWG Wire, Rear Mount Flange Assembly, without Gasket, Black |
| Application | Power, Wire-to-Wire |
| Comments | For Inside Panel Mount Application; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS) |
| Product Name | MX150L |
| UPC | 822348543472 |

Agency

| | |
|----|---------|
| UL | E152602 |
|----|---------|

Physical

| | |
|--------------------|----|
| Circuits (maximum) | 10 |
|--------------------|----|

| | |
|-------------------------------|----------------|
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Plug |
| Glow-Wire Capable | No |
| Lock to Mating Part | Yes |
| Net Weight | 18.050/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 5.84mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +125°C |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|----------------------------|--------------|
| MX150L Receptacle Housings | <u>19418</u> |

Use with Part(s)

| Description | Part Number |
|---|------------------|
| MX150L Gasket for 10 Circuit Plug Housing with Flange | <u>194270029</u> |
| MX150L Male Terminals and Circuit Voiding Keys | <u>19417</u> |