

General Information

Extended Product Type:	216-P6
Product ID:	2CMA193501R1000
EAN:	7392696935012
Catalog Description:	Plug, 6h, 16A, IP44, 2P+E
Long Description:	Plug, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 2-poles+earth, 50 - 60 Hertz, color code blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Plugs

Ordering

EAN:	7392696935012
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	63 mm
Product Net Height:	63 mm
Product Net Length:	125 mm
Product Net Depth:	63 mm
Product Net Weight:	0.11 kg

Container Information

Package Level 1 Width:	138 mm
Package Level 1 Length:	120 mm
Package Level 1 Height:	285 mm
Package Level 1 Gross Weight:	0.11 kg
Package Level 1 EAN:	7392696935012
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, compression gland
Cable Cross-Section:	1.0 ... 2.5 mm ²
Color:	Blue
Degree of Protection:	IP44
Enclosure Material:	Polyamide
Frequency (f):	60 Hz
Function:	Plug
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216-P6
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	P
Product Name:	Industrial Plug
Protection Type:	Splashproof
Rated Current (I _n):	16 A
Rated Voltage (U _r):	200 ... 250 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Plugs
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2416161

UNSPSC: 39120000

