

VDE 2170 5,5

VDE Screwdriver

for slotted head screws

Code	ETIM
1612271	EC000158
EAN	UNSPSC
4010886826041	27-11-17-01
Country of origin	eCl@ss
Slovenia	21-04-04-01
Customs tariff number	
82054000	



Article description

- Individually tested, VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900, fully insulated blade
- Tip as per DIN ISO 2380-1 Form A
- 3-component Power-Grip³ handle with suspension hole
- Ergonomic handle shape for accurate, non-tiring work
- Positive connection of handle and blade for optimum power transmission
- Type of drive marked at the end of the handle
- Blade of galvanised molybdenum-vanadium steel

Article information

Contents (Qty of pieces)	1	Impact cap	no
Version/Execution	with hanging hole	Cap rotatable	no
Net weight [kg]	0,095 kg	Anti-magnetic	no
Total length [mm]	225 mm	Ball head	no
Total width [mm]	33 mm	Handle available	yes
Total height [mm]	29 mm	Isolated	yes
Material	Molybdenum-vanadium-steel	Corrosion Protected	no
Blade length	125 mm	Colour coding	no
Standard	EN 60900/IEC60900	Unit-tested	yes
Blade width [mm]	5,5 mm	Handle design	3-component grips VDE insulated up to 1000 V
Low sparking design	no	Output tip reference standard	DIN ISO 2380-1 - Form A
Blade shape	Round	Drive hexagon	no
Roll protection	yes	Blade thickness	1 mm