

Product Information



PVO080x35-Ø12

EAN 4031582321180

Wheel centre made of Polypropylene, Tread: solid rubber, black, plain bearing

Technical Data	
Wheel diameter	80 mm
Width of Tread	35 mm
Axle Hole Ø	12 mm
Hub length	44.4 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	0.144 kg
Load capacity	70 kg
Load capacity (static)	140 kg
Hardness of tread	A 85 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

