



ENGLISH

Datasheet

RS Pro Stainless Steel Hex Bolt, M6 x 45mm

RS Stock No: **917-6235**



Product Details

RS Pro hex bolt is of size M6 x 45 mm, features A2, 304 stainless steel construction for durability. This hex bolt is partially threaded and can be used with a nut or in a tapped hole. This bolt is tightened with a wrench. The metric threaded hex bolt meets DIN 931 standards.

Features and Benefits

- Good corrosion resistance
- Recyclable
- Non-magnetic
- It is suitable for machine repairs and outdoor applications
- Threaded in accordance with DIN 931

**Specifications:**

Material	Stainless Steel
Grade	304
Length	45 mm
Stainless Steel Type	304 (A2)
Thread Pitch	1
Thread Size	M6
Head Height	4 mm
Specification	DIN 931
Width Across Corners	11.05 mm
Width Across Flats	10 mm