

D 19 IMU-10

1/2" Socket set

27 pieces

Code 6140090 ETIM EC002209
 EAN 4010886614006 UNSPSC 27-11-17-03
 Country of origin Germany eCl@ss 21-04-02-05
 Customs tariff number 82042000



Article description

- With forged, tempered hexagon (No. 19) or bi-hexagon (No. D 19) UD profile sockets, hand-operated
- With accessories made from vanadium steel 31CrV3
- With robust lever-change reversible ratchet, with push-button release
- In GEDORE blue sheet steel case
- Dimensions: 425 x 277 x 55 mm

Article parts list

Ratchet ,1993 U-10 T ,Inserts ,D 19 10 11 12 13 14 ,15 17 19 22 24 27 30 ,IN 19 5 6 7 8 10 12 14 ,15 19 8 10 ,ICS 19 2 3 ,Accessories ,1/2"
 Extension 1990-5-10 ,Universal joint 1995

Article information

Contents (Qty of pieces)	27	Total height [mm]	55 mm
Net weight [kg]	6,8 kg	Total depth [mm]	277 mm
Total length [mm]	277 mm	Drive connector square (male)	1/2"
Total width [mm]	425 mm	Drive connector square (male)	12,5 mm