

IN 19 L 8-120

Screwdriver bit socket 1/2"

Code 6157810 ETIM EC002157
EAN 4010886615782 UNSPSC 27-11-17-01
Country of origin Germany eCl@ss 21-04-04-02
Customs tariff number 82079030



Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated

Article information

| | | | |
|--|-----------------------|--------------------------------------|---|
| Contents (Qty of pieces) | 1 | Drive connector square female [inch] | 1/2" |
| Net weight [kg] | 0,109 kg | Standard | DIN 7422 DIN 3120 - C 12,5 ISO 1174 |
| Total length [mm] | 120 mm | Width across flats l [mm] | 8 |
| Total width [mm] | 22,5 mm | Backup | Ball Catching Cricket |
| Surface | chrome-plated | Tip length | 82,0 mm |
| Material | Chrome-vanadium steel | Insert Ø Actuator | 22,5 mm |
| Drive connector square female (metric) | 12,5 mm | | |