



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	User manual
--------------------	-------------

### Physical

Cable length	1.22 m
Depth	25.6 cm
Height	20 cm
Net weight	6 kg
Width	11.5 cm

### Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	IEC 60320 C14
Input voltage limits	140...300 V
Switching current capacity	7 A
Input voltage	230 V

### Output

Rated power in W	390 W
Maximum configurable power in W	390 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains
UPS type	Line interactive
Wave type	Stepped approximation to a sinewave
Nb of power socket outlets	4 IEC 60320 C13 1 IEC Jumpers
Output voltage	230 V

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage altitude	0.00...9144.00 m
Acoustic level	45 dBA

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	6 h
Number of battery replacement quantity	1
Liquid value	0

## Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rate	273 J
Data line protection	RJ11 modem/fax/DSL protection (two wire single line)

## Packing Units

Package 1 Weight	6.5 kg
Package 1 Height	27.5 cm
Package 1 width	29.5 cm
Package 1 Length	34 cm
SCC14	10731304315800

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------