

5551305

UST Detail Brush, 205 mm, Soft, White



The UST Detail Brush is designed for detail cleaning in dry environments where soft bristles are useful and hygiene is critical, such as when allergens are a risk. Also useful as a pastry or glazing brush in food handling applications, this brush delivers all the advanced benefits of Vikan's other Ultra Safe Technology (UST) cleaning tools.

Technical Data

Item Number	5551305
Visible bristle length	57 mm
Material	Polypropylene Polyester
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Patent Pending No.	PA201270087, PA201270088
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	5290 Pcs
Quantity Per Layer (Pallet)	180 Pcs.
Box Length	265 mm
Box Width	150 mm
Box Height	75 mm
Length	205 mm
Width	30 mm
Height	10 mm
Gross Weight	0,04 kg
Net Weight	0,03 kg
Cubik metre	0,0001 M3
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. drying temperature	100 °C
Min. usage temperature	-20 °C
Max. pH-value in Usage Concentration	10,5 pH
Min. pH-value in usage concentration	2 pH
Recycling Mark 7	Yes
Gtin-13 Number	5705022009233
GTIN-14 Number (Box quantity)	15705028009319
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact