

## 1U Cable Dump Panel 24 Slot



### **1U Cable Dump Panel Management Bar - 24 slot (MCMDMP)**

This 24 slot horizontal cable dump panel with snap on lid enables the installer to maintain neat cabling in 19" racks and cabinets in accordance with cabling standards.

#### **Features**

- 1U cable dump panel with 24 slots top and bottom, suitable for cables with OD up to 8.2mm
- Easy-fit push fit lid provides easy access to patch leads
- Designed to give extra support for patch leads
- Enables neat and professional organisation of patch cables in accordance with ISO and EIA/TIA standards
- Rear pass-through feature offers the option of front to back cable management
- Supplied with a set of 4 x M6 cage nuts, bolts and washers

#### **Specifications**

- Weight: approx. 516g (including primary packaging)
- Dimensions: 513 x 92 x 55mm (including primary packaging)
- Material: Open slot trunking: fire retardant PVC,  
Snap on lid: fire retardant PVC  
Mounting bar: 1.5mm powder coated cold rolled steel
- Finish: black

**Packaging:** Packed in individual cardboard boxes and then in cartons of 13

**EAN:** 5055386511751

**Commodity Code:** 85177090

**Country of Origin:** China

ROHS Compliant

Code: MCMDMP

