

**Z-series
ZQV 6N/2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	ZQV 6N/2
Order No.	1985740000
Version	Z-series, Cross-connector, No. of poles: 2
GTIN (EAN)	4050118370362
Qty.	60 pc(s).

**Z-series
ZQV 6N/2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	13.7 mm	Width (inches)	0.539 inch
Height	34.11 mm	Height (inches)	1.343 inch
Depth	3.1 mm	Depth (inches)	0.122 inch
Net weight	2.37 g		

Material data

Material	Wemid	Colour	Orange
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

Dimensions

Pitch in mm (P)	8 mm
-----------------	------

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	eClass 6.2	27-14-11-40
eClass 9.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	2434520000 BED-ANL.ZQV A REIHE.pdf