

## Data sheet for Line filter

MLFB-Ordering data

6SE6400-2FA00-6AD0



Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Rated data

#### Input

Number of phases	3 AC
Line voltage	200 ... 480 V

#### Output

Rated current	6.0 A
---------------	-------

### Mechanical data

#### Dimensions

Width	73.0 mm
Height	200.0 mm
Depth	43.5 mm
Degree of protection	IP20 / UL open type
Net weight	0.5 kg

### Connections

#### Line side

Version	screw-type terminal
Conductor cross-section	1,0 ... 2,5 mm <sup>2</sup>

#### Load side

Version	Pigtail
Cable length	0.46 m

#### PE connection

Version	M4 stud
---------	---------

### Standards

Compliance with standards	CE / UL
---------------------------	---------