



PRODUCT-DETAILS

EH04-20N

EH04-20N Auxiliary Contact - 0 NO - 0 NC - Auxiliary Circuit 50 Hz



概要信息	
产品型号	EH04-20N
产品ID	1SAE901901R1020
欧洲商品编号(EAN)	4013614527623
目录说明	EH04-20N Auxiliary Contact - 0 NO - 0 NC - Auxiliary Circuit 50 Hz
详细描述	The EH04 are auxiliary contact blocks which can be used in combination with all the new ESB..N and EN..N installation contactors. These devices are available in 2 different contact configurations and no tool is needed for their assembling.

订货信息	
最小起订量	1 piece
海关关税号	85369010

Popular Downloads	
数据手册, 技术资料	2CDC103051C0201
说明书和手册	2CDC103043M6801

尺寸

产品净宽	9 mm
产品净深	65 mm
产品净高	85 mm
产品净重	0.04 kg

技术参数

额定工作电压	Auxiliary Circuit 500 V AC
额定频率 (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz
额定冲击耐受电压 (U _{imp})	Auxiliary Circuit 4 kV
额定绝缘电压 (U _i)	500 V
极数	2
防护等级	IP20
拧紧力矩	Auxiliary Circuit 0.9 N·m
剥线长度	Auxiliary Circuit, Top Terminals (1x 1.5) 7 mm Auxiliary Circuit, Top Terminals (1x 2.5 ... 4) 17 mm Auxiliary Circuit, Top Terminals (2x 1.5) 17 mm Auxiliary Circuit, Bottom Terminals (1x 1.5) 7 mm Auxiliary Circuit, Bottom Terminals (1x 2.5 ... 4) 9 mm Auxiliary Circuit, Bottom Terminals (2x 1.5) 9 mm
推荐的螺丝刀	Auxiliary Circuit Pozidriv 1
标准	IEC/EN 60947-5-1
辅助触点NC数量	0
辅助触点NO数量	2
主触点NC数量	0
主触点NO数量	0
产品	Auxiliary Contact
适用于	ESB16..N ESB20..N ESB25..N ESB40..N ESB63..N EN20..N EN25..N EN40..N ESB100..N
适用产品系列	Installation Contactors

UL/CSA适用的技术参数

最高工作电压UL/CSA	600 V AC
辅助电路连接容量 UL/CSA	Stranded 18-12 AWG
拧紧力矩UL/CSA	Auxiliary Circuit 8 in·lb

环境条件

周围环境温度	Operation -25 ... +55 °C Storage -40 ... +80 °C
额定发热电流（自由空	Auxiliary Circuit 6 A

气) (I_{th})

允许的最高工作海拔	2000 m
抗机械冲击符合IEC 60068-2-27标准	11 ms Pulse 15g
耐振动符合IEC 60068-2-6标准	5g 3 ... 150 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS信息	2CMT2021-006277
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Consumer
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）

ABS认证	1SAA920000-0101
CB认证	1SAA920006-2001
CQC认证	CQC2017010304980330
Declaration of Conformity - CCC	2020980305001265
符合性声明 - CE	1SAD101100-3301
Declaration of Conformity - UKCA	1SAD201100-3301
DNV认证	1SAA920000-0306
EAC认证	1SAA920002-2701
RINA认证	1SAA920000-0801
UL认证	E191658-19960301

包装信息

1级包装宽度	87 mm
1级包装长度	18 mm
1级包装高度	69.5 mm
1级包装 总重	0.05 kg
1级包装 EAN	4013614527821
1级包装单元	box 1 piece

分类

对象分类代码	K
ETIM 5	EC000041 - Auxiliary contact block
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
e级	V11.0 : 27371302
UNSPSC	39121522
E-Number (Finland)	3707817

E-Number (Norway)	4190271
E-Number (Sweden)	3210568
IDEA 粒度分类代码 (IGCC)	4743 >> Auxiliary contact block

分类

低压产品及系统 → 控制产品 → 接触器 → 建筑用接触器
低压产品及系统 → 线路保护产品 → Command and Signalling Devices → 建筑用接触器

