

Professionally approved products.

Datasheet

20 → 600mm Compact Gasket Cutter

RS Stock number [2820935](#)



Description

Precision made hand tool for the efficient on-site cutting of circular flange gaskets made from compressed fibre jointing, rubber and cork-elastomer sheet.

Features

- Easy to use hand tool.
- Readily adjusts for diameters from 20mm (13/16 inch) up to 600mm (24 inch).
- Longer extension bar available for diameters up to 900mm (35 inch).
- Dual metric/inch calibration.
- Cuts compressed fibre jointings up to 5mm thickness.
- Cuts rubber and cork-elastomer sheets up to 12mm thickness.

Specification

- Kit Contents: Main Cutting Assembly; Extension Bar; Cutting Board; Blades; Hex Keys; Instruction Leaflet; Storage Holdall
- Maximum Cutting Diameter: 600mm
- Maximum Thickness: 12.5mm
- Minimum Cutting Diameter: 20mm