

Datasheet

RS Pro M63 Black Nylon Cable Gland With Lock Nut, 34 to 44mm Cable Dia Range, IP68

RS Stock No: **669-4686**



Product Details

RS Pro cable gland in black colour, has a thread size of M63. It has a cable diameter ranging from 34 to 44 mm. The cable made of plastic is IP68 rated. This nylon cable gland is supplied completely with lock nut and entry thread seal.

Features and Benefits

- Manufactured from UL approved nylon 66
- Flammability rating to UL 94V-2
- Provides watertight seal to IP68
- Offers strain relief and protection for cables

**Specifications:**

Cable Diameter Range	34 to 44 mm
Colour	Black
IP Rating	IP68
Locknut Included	Yes
Material	Nylon 66
Maximum Cable Diameter	44 mm
Maximum Operating Temperature	+85°C
Minimum Cable Diameter	34 mm
Minimum Operating Temperature	-60°C
Operating Temperature Range	-60 to +150°C
Standards Met	UL 94V-2
Thread Size	M63