

## FLAT BASE TOTE BOXES

### 21-701-xxxx

Wez standard containers are designed for euro pallets 1200x800 or 1200x1000.



### Product specifications

|                      |   |
|----------------------|---|
| Material:            | Conductive polypropylene (carbon-loaded)                                    |
| Colour:              | Black   |
| ESD Marking:         | All containers marked with ESD sign   |
| Surface resistance:  | $\leq 10^4$ Ohm   |
| Usage temperature:   | 80°C. Please note that depending of load, deformation can appear from 50°C. |
| Stackability:        | All containers may be stacked together in a wide range of configurations.   |
| Average stack load:  | 500 kg  |
| Standard compliance: | IEC 61340-5-1 / RoHS Directive (2002/95/CE)                                 |

### Features and Part Number

| Part Number                                | Ext. Dim. (mm)  | Int. Dim. (mm)  | Usable depth (mm) | Capacity (litre) | Weight (gram) |
|--|-----------------|-----------------|-------------------|------------------|---------------|
| 21-701-0000                                | 200 x 150 x 145 | 155 x 106 x 142 | 129               | 2.7              | 375           |
| 21-701-0010                                | 300 x 200 x 100 | 254 x 154 x 96  | 83                | 3.75             | 520           |
| 21-701-0015                                | 300 x 200 x 145 | 254 x 154 x 141 | 128               | 5.5              | 720           |
| 21-701-0020                                | 400 x 300 x 53  | 354 x 254 x 49  | 40                | 4.4              | 540           |
| 21-701-0025                                | 400 x 300 x 100 | 354 x 254 x 96  | 83                | 8.7              | 1030          |
| 21-701-0030                                | 400 x 300 x 145 | 354 x 254 x 141 | 128               | 12.8             | 1200          |
| 21-701-0035                                | 400 x 300 x 212 | 354 x 254 x 208 | 195               | 19.2             | 1610          |
| 21-701-0040                                | 400 x 300 x 278 | 354 x 254 x 274 | 261               | 25.2             | 1975          |
| 21-701-0045                                | 400 x 300 x 320 | 354 x 254 x 316 | 303               | 29.0             | 2100          |
| 21-701-0055                                | 600 x 400 x 100 | 554 x 354 x 96  | 83                | 19.0             | 1650          |
| 21-701-0060                                | 600x 400 x 145  | 554 x 354 x 141 | 128               | 28.0             | 2050          |
| 21-701-0065                                | 600 x 400 x 212 | 554 x 354 x 208 | 195               | 41.0             | 2550          |
| 21-701-0070                                | 600 x 400 x 278 | 554 x 354 x 273 | 260               | 55.0             | 3070          |
| 21-701-0075                                | 600 x 400 x 320 | 554 x 354 x 316 | 303               | 62.0             | 3400          |
| 21-701-0080                                | 600 x 400 x 412 | 554 x 354 x 407 | 393               | 82.0             | 4605          |
| <b>Light version (between 40% and 60%)</b> |                 |                 |                   |                  |               |
| 21-700-0100                                | 400 x 300 x 145 | 354 x 254 x 141 | 128               | 12.8             | 700           |
| 21-700-0105                                | 600 x 400 x 145 | 554 x 354 x 141 | 128               | 28.0             | 1230          |