



### Main

Range	Actassi
Product or component type	Fan
Device application	Electronic application
Accessory / separate part type	Ventilation plate
Cable gland type	With 3 fans Ventilated
Noise level	34 dB
Quantity per set	Set of 1

### Complementary

Range compatibility	Actassi VDA Actassi VDS
Product compatibility	SF roof for Actassi plates
Air flow	170 m3/h
Device composition	Fixing elements 1 plate 1 2 m power cord
Material	Plate: galvanised steel
Mounting location	On outside of the roof
Fixing mode	By screws
Width	420 mm fixing centers:

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------