
## 8065265 DFPD-900-RP-90-RD-F14 Semi-rotary drive - Series: All



# 8065265 DFPD-900-RP-90-RD-F14 Semi-rotary drive - Series: All

| Pos. | Part no. | Type | Note | Qty. | Unit |
|---|---|---|---|---|---|
| A | 8229257 | DFPD-900-.. REV1<br>Set of wearing parts | Spare parts: 3, 5, 6, 7, 8, 12, 14, 15, 17, 19, 20, 21, 22, 23, 25, 26, 28, 29<br>Replacing the wearing parts<br>Attention, please order position 30 as well | 1 | PC |
| 1 | | ISO 4017-M12X45-A2-70<br>Hexagon head screw | Not available<br>Tightening torque 65 Nm / 47.9 lbf ft | 8 | PC |
| 2 | | ISO 7092-12-200HV-A2<br>Disc | Not available | 8 | PC |
| 3 | | DIN 6797-J-13-A2-70<br>Toothed disc | Not available separately, see position A | 8 | PC |
| 4 | | DFPD-900-D/S<br>End cap | Not available | 2 | PC |
| 5 | | 183,74X3,53-N-NBR70<br>O-ring | Not available separately, see position A | 2 | PC |
| 6 | | DFPD-900-../T6<br>Slip ring | Not available separately, see position A<br>Repair note: Slip_ring | 2 | PC |
| 7 | | 164,47X6,99-N-NBR70<br>O-ring | Not available separately, see position A | 2 | PC |
| 8 | | DFPD-900-../T6<br>Slide element | Not available separately, see position A | 2 | PC |
| 9 | | DFPD-900-90<br>Piston | Not available<br>Lubricate with SYNTHY POLYMER 402/2 during assembly | 2 | PC |
| 10 | | DFPD-700/900<br>Plug | Not available | 2 | PC |
| 11 | | ISO 4762-M5X16-A2-70<br>Socket head screw | Not available<br>Tightening torque 7 Nm / 5.2 lbf ft | 2 | PC |
| 12 | | J-5,1-A2-70<br>Toothed disc | Not available separately, see position A | 2 | PC |
| 13 | | DFPD-700/900-AN<br>Sub-base | Not available | 1 | PC |
| 14 | | B-21X2-N-NBR70<br>O-ring ISO3601 | Not available separately, see position A | 2 | PC |
| 15 | | DIN 471-48X1,75-A2<br>Retaining ring | Not available separately, see position A | 1 | PC |
| 16 | | DIN 988-48X60X2-A2<br>Shim | Not available | 1 | PC |
| 17 | | DFPD-900-../T6<br>Slip ring | Not available separately, see position A<br>Repair note: Slip_ring | 1 | PC |
| 18 | | DFPD-900-90-F1012-AN<br>Housing | Not available<br>Lubricate with SYNTHY POLYMER 402/2 during assembly | 1 | PC |
| 19 | | B-15,47X3,53-N-NBR70<br>O-ring ISO3601 | Not available separately, see position A | 2 | PC |
| 20 | | 16,3X30X5-1.4301<br>Ring | Not available separately, see position A | 2 | PC |
| 21 | | ISO 4032-M16-A2-70<br>Hex nut | Not available separately, see position A<br>Tightening torque 177.5 Nm / 130.9 lbf ft | 2 | PC |
| 22 | | DFPD-900/1200<br>adjusting screw | Not available separately, see position A | 2 | PC |
| 23 | | DFPD-900-../T6<br>Slip ring | Not available separately, see position A<br>Repair note: Slip_ring | 1 | PC |
| 24 | | DFPD-900-90<br>Cam | Not available | 1 | PC |
| 25 | | B-40,87X3,53-N-NBR70<br>O-ring ISO3601 | Not available separately, see position A | 1 | PC |

| Pos. | Part no. | Type | Note | Qty. | Unit |
|---|---|---|---|---|---|
| 26 | | DFPD-900-../T6<br>Slip ring | Not available separately, see position A<br>Repair note: Slip_ring | 1 | PC |
| 27 | | DFPD-900-KT27<br>Shaft | Not available<br>Lubricate with SYNTHY POLYMER 402/2 during assembly | 1 | PC |
| 28 | | DFPD-900-../T6<br>Slip ring | Not available separately, see position A<br>Repair note: Slip_ring | 1 | PC |
| 29 | | B-66,27X3,53-N-NBR70<br>O-ring ISO3601 | Not available separately, see position A | 1 | PC |
| 30 | 684474 | LUB-KC1 SILIKONFREI 20ML<br>Lubricating grease | Not included in wearing-parts kit | 2 | PC |