



## DCF622P2

### 18V 5.0Ah Self-Drilling Screwdriver Kit

#### Selling Proposition

- 18V XR Li-Ion BRUSHLESS Self-Drilling Screwdriver for quick fitting of metal roofing and other sheet metal applications
- High-torque 2000rpm BRUSHLESS motor drives screws up to 6.15mm diameter efficiently and effectively offering maximum runtime and a compact tool
- 5.0Ah High Capacity battery pack coupled with the BRUSHLESS motor offers eXtreme Runtime and compatability with the rest of your 18V XR tools
- One of the lightest and most compact tools on the market - it ensures that you can work comfortably
- Robust and durable design means that the tool is jobsite tough
- Versa-clutch delivers repeatable screw setting with minimum fuss

#### Standard Equipment

- 2 x 18V 5.0Ah XR Li-Ion battery packs
- Multi-voltage XR charger
- TSTAK 2 Kitbox

#### Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)
- 3 year limited warranty

Specifications	
Max Torque	11/34 Hard/Soft Nm
Power Output	850 Watt
No Load Speed	0 - 2000 rpm
Max. Screw Diameter	6.15 mm
Tool Holder	(Hex) 6.35 mm
Weight	1.97 kg
Length	255 mm
Height	265 mm