



Main

Range	Resi9
Product or component type	Partition wall
Range compatibility	Opale Resi9
Standards	NFC 15-100 NF EN 50085-2-1

Environment

IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
Height	2600 mm
Colour	White (RAL 9003)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.