



ENGLISH

Datasheet

RS PRO 60 Degree C Masking Tape



Representative Image Only.

Specifications:

Color: White

Temperature resistant: 60°C, 0.5H

Weight: 90±2 g/m²

Thickness: 150±5micron

Tensile strength: 42±5 N/25mm

Elongation: 12±2%

10/05/2017

Tack (steel ball): 12±2 #

Holding power: 2±0.5hour

Peel Strength at the beginning: 7±0.5 N/25mm

Peel Strength after stable: 6.5±0.5 N/25mm

Testing environment: Temperature 23±2°C, Humidity 60±5RH

Size:

RS Article No:	Size
131-1973	19mm x 50M
131-1974	25mm x 50M
131-1975	38mm x 50M
131-1976	50mm x 50M
131-1977	75mm x 50M

Features:

Based on good quality white crepe paper, it is easy -tearing, has good adhesion, 60 degree C temperature resistant, no residue, high adhesive strength, excellent flexibility, easy to clean and environment friendly. Suitable for decorating, painting, spray painting, or providing general protection to surfaces when decorating.