



**Product Datasheet**

**English**

**Stock No:**

**Digital Hygro-Thermometer**



## Production introduction

This is a desktop or wall type temperature and humidity meter, with high precision and quality digital sensor (14-bit resolution temperature, 12-bit resolution humidity), with low battery indication, °C/°F unit switching, ultra low power consumption, 2pcs 1.5V AA batteries available to continue working for 7-8 months.

## Production Feature

1. Have clear and easy-to read LCD screen.
2. Temperature readings are in °C and °F, both can be optionally replaced.
3. When the battery voltage is lower than 2.4V, there will be low battery icon.
4. When working at low power, the LCD can also clearly show.
5. The overall working current is small, and a pair of new alkaline AA batteries can work for 6~7 months.
6. Comfort indicator function, different temperature or humidity environment, LCD will be in the color comfort scale corresponding instructions.
7. This measuring instrument is simple and easy to operate.

## Specifications

<b>Range</b>
Temperature Range: -10 to 60°C (14 to 140°F)
Humidity Range: 0 to 99%
<b>Resolution</b>
Temperature Resolution: 0.1°C/°F
Humidity Resolution: 0.1%RH
<b>Precision</b>
Temperature Precision: ±1°C(±1.8°F)
Humidity Precision: ±4%RH

Accessories: battery, gift box and carrying case.