


Base cover lateral H: 100 mm D: 800 mm



Model	
product brand name	SIVACON S4
product designation	Base covers
design of the product	Lateral
design of cabinet base element	for standard frame
Suitability	
suitability for interaction cable assignment	No
suitability for use for outside use	No
Appearance	
RAL color number	sim. RAL 5020
color	blue green basic
product component	module incl. mounting material
• on delivery	
• ventilation	No
Mechanical Design	
height	100 mm
width	12 mm
depth	800 mm
installation width for cabinet installation	12 mm
installation depth for cabinet installation	800 mm
net weight	2.36 kg
material	sheet-steel
material thickness	1.5 mm
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Confirmation](#)

other	Environment
Miscellaneous	Environmental Con- firmations
	Environmental Con- firmations

Further information
Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ1010-8BA01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ1010-8BA01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ1010-8BA01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/4/2025 

