

FR06 - Bizflame Industry Two Tone FR Trousers

Collection: Bizflame™ Industry

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Industry: 80% Cotton, 19% Polyester, 1% Carbon Fibre, 340g

Outer Carton: 16

Product information

Contemporary design using durable fabric, combining comfort and functionality. The hardwearing fabric is tough enough to withstand the rigours of industrial laundry, retaining shape and colour over the lifetime of the trousers.

Bizflame™ Industry

Bizflame™ Industry has been developed to perform in the toughest conditions. Ideal for industries such as oil and gas where durability is a must, Bizflame™ Industry is certified to a range of EN standards offering optimum protection in a range of hazardous situations. Styles in this range are metal free, minimising the risk of static electricity hazards and of damage to surfaces. Bizflame™ Industry FR polyester has been made from recycled fibres thereby reducing the production carbon footprint and working towards a sustainable future.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 11 CAL/CM², ATPV 13 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 13034 Type 6

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV 16 CAL/CM² (HAP 83.7kJ))



Features

- Industrial laundry wash at 75°C and tunnel dry at 155°C
- Protection against radiant, convective and contact heat
- Rule pocket
- Certified protection against molten metal splash
- Extendable leg length (31" to 33")
- Non-magnetic - nickel and ferrous free
- 8 pockets for ample storage
- Two tier knee pad pockets allowing two positioning options
- Sew on flame resistant industrial wash tape
- 40+ UPF rated fabric to block 98% of UV rays
- Side elastic waist for ultimate wearer comfort

FR06 - Bizflame Industry Two Tone FR Trousers

Commodity Code: 6203421100

Test House

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)

Sebenhirtenstrasse 12A

1230, Austria

Contact: Marion Pfeiler

Cert No: VN625 154930

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)

Sebenhirtenstrasse 12A

1230, Austria

Contact: Marion Pfeiler

Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
FR06RER30	Red	43.0	28.0	58.0	0.8820	0.0698	5036108407743	25036108893151
FR06RER32	Red	43.0	28.0	58.0	0.9100	0.0698	5036108407750	25036108893168
FR06RER33	Red	43.0	28.0	58.0	0.9740	0.0698	5036108407767	25036108893175
FR06RER34	Red	43.0	28.0	58.0	0.9280	0.0698	5036108407774	25036108893182
FR06RER36	Red	43.0	28.0	58.0	0.9760	0.0698	5036108407781	25036108893199
FR06RER38	Red	43.0	28.0	58.0	1.0300	0.0698	5036108407798	25036108893205
FR06RER40	Red	43.0	28.0	58.0	1.0100	0.0698	5036108407804	25036108893212
FR06RER41	Red	43.0	28.0	58.0	1.0400	0.0698	5036108407811	25036108893229
FR06RER42	Red	43.0	28.0	58.0	1.0800	0.0698	5036108407828	25036108893236
FR06RER44	Red	43.0	28.0	58.0	1.0700	0.0698	5036108407835	25036108893243
FR06RER46	Red	43.0	28.0	58.0	1.1200	0.0698	5036108407842	25036108893250