


543-...

Electronic cutting pliers, ogival head, extra-fine nose

ELECTRONIC



DESCRIPTION

Electronic cutting pliers, ogival head, extra-fine nose

Fine nose for reworking circuits when debugging. Anti-static-electricity arms.

NF ISO 9654

SPECIFIC DATA

Designation	ELECTRONIC PLIER CUTTER SMALL
Sales reference	543-T
L (mm)	105
Weight (g)	55
Cutting	Axial
Ø max. mm Cu-Ni	1.2
Ø max. mm Fe 30HRC	0.6
Ø max. mm hard steel	-
L1 (mm)	9
Retainer	No
Ø max. mm Cu	-
Warranty	0