

Wiha PicoFinish.

The comfortable precision screwdriver.

For TORX PLUS® screws.



267PIP PicoFinish TORX PLUS® screwdriver.

Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for fine and delicate fastening tasks for electronics, precision mechanics, model-making and hobby activities.

Extra: The stronger profile of the TORX PLUS® tip allows up to 25% extra torque than the TORX® profile.

Order-No.	●	↔	●	↔	↔	↔
29100	4IP	40	2.5	134	9	10
29101	5IP	40	2.5	134	9	10
29102	6IP	40	2.5	140	18	10
29103	7IP	40	2.5	140	18	10
29104	8IP	40	2.5	140	18	10
29105	9IP	50	3.0	150	18	10
29106	10IP	50	3.0	150	18	10
29107	15IP	60	3.5	160	18	10
29108	20IP	60	4.0	160	18	10



NEW

267PIPR PicoFinish TORX PLUS® security screwdriver (tamper-resistant). Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for repairing smartphones, tablets, notebooks, etc.

Attention: The guarantee and warranty conditions of the device manufacturer must be observed!

Security profile - sold only to authorised customers. Written proof of authorisation must be received.

Order-No.	●	↔	●	↔	↔	↔
38837	1IPR	40	2.5	134	9	10
38838	2IPR	40	2.5	134	9	10
38839	3IPR	40	2.5	134	9	10
38840	4IPR	40	2.5	134	9	10
38842	5IPR	40	2.5	134	9	10
38843	6IPR	40	2.5	140	18	10

For hex socket screws.



263P PicoFinish hex screwdriver.

Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for fine and delicate fastening tasks for electronics, precision mechanics, model-making and hobby activities.

Order-No.	●	↔	●	↔	↔	↔
00519	0.7	40	0.028	134	9	10
00520	0.9	40	0.035	134	9	10
00521	1.3	40	0.05	134	9	10
00522	1.5	50	-	144	9	10
00523	2.0	50	5/64	150	18	10
00524	2.5	60	-	160	18	10
00525	3.0	60	-	160	18	10

263P Zoll PicoFinish hex screwdriver. Inch sizes.

Handle with rotating cap and rapid-turning zone.

Order-No.	●	↔	↔	↔	↔
00526	1/16	50	144	9	10
00528	3/32	60	160	18	10
00530	7/64	60	160	18	10
00527	1/8	60	160	18	10



264P PicoFinish ball end hex screwdriver.

Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for fine and delicate fastening tasks for electronics, precision mechanics, model-making and hobby activities.

Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	●	↔	●	↔	↔	↔
00531	1.3	40	0.05	134	9	10
00532	1.5	50	-	150	18	10
00533	2.0	50	-	150	18	10
00534	2.5	60	-	160	18	10
00535	3.0	60	-	160	18	10

264P Zoll PicoFinish ball end hex screwdriver. Inch sizes.

Handle with rotating cap and rapid-turning zone.

Order-No.	●	↔	↔	↔	↔
00537	1/16	50	150	18	10
00541	5/64	50	150	18	10
00539	3/32	50	150	18	10
00542	7/64	60	160	18	10
00538	1/8	60	160	18	10
00543	9/64	60	160	18	10
00540	5/32	60	160	18	10