

MAG-LED™ Technology

MAGLITE® ML125® LED RECHARGEABLE

DESCRIPTION

The Maglite® ML125® LED Rechargeable is a versatile torch that can be powered by either a rechargeable NiMH battery or 3 C-Cell alkaline batteries. It is also possible to select from multiple function sets, so the user has choices in both how the torch is powered and how it performs. It has a sleek profile, bright

adjustable beam and a multi-mode electronic switch.

PACKS

BOX INCLUDES:

ML125® LED torch, NiMH battery, charging cradle, UK wall plug.

PRODUCT CODES

BOXED:

BLACK – ML125-35014

AVAILABLE COLOURS



Black

FL 1 STANDARD						HIGH	LOW
							
258m	186 LUMENS	16725cd	1m	8h30min	30h		
BEAM DISTANCE	LUMENS	PEAK BEAM INTENSITY	WATER RESISTANT	DROP RESISTANT	RUN TIME		

