

D

C

B

A

D

C

B

A

注記

1 材料：ガラス入り熱可塑性ポリエステル樹脂

黒	7-178128-3以外
オレンジ	7-178128-3
色	製品番号

~~△~~ハウジング全面にテフロン塗装のこと

3 製品規格：108-5349

4 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

NOTE






1 MATERIAL:GLASS FIELD THERMO PLASTIC,POLYESTER

BLACK	EXCEPT 7-178128-3
ORANGE	7-178128-3
COLOR	PART NUMBER


~~△~~TO COAT ALL SURFACE OF HOUSING WITH TEFLON

3 PRODUCT SPEC.: 108-5349

4 THE SHAPE,SIZE AND POSITION OFTHE CHARACTER SHOW THE OUTLINE THEY DON'T SHOW DETAILS



								2-178128-6
								1-178128-6
								2-178128-5
								1-178128-5
OBSOLETE	△	△	Y	15.24	24.32	29.18	34.78	6-178128-4
OBSOLETE	△	△	X	15.24	24.32	29.18	34.78	5-178128-4
			Y	15.24	24.32	29.18	34.78	2-178128-4
			X	15.24	24.32	29.18	34.78	1-178128-4
OBSOLETE	△	△	X	10.16	19.24	24.10	29.7	7-178128-3
OBSOLETE	△	△	Y	10.16	19.24	24.10	29.7	6-178128-3
OBSOLETE	△	△	X	10.16	19.24	24.10	29.7	5-178128-3
			Z	10.16	19.24	24.10	29.7	3-178128-3
			Y	10.16	19.24	24.10	29.7	2-178128-3
			X	10.16	19.24	24.10	29.7	1-178128-3
OBSOLETE	△	△	Y	5.08	14.16	19.02	24.62	6-178128-2
OBSOLETE	△	△	X	5.08	14.16	19.02	24.62	5-178128-2
			Y	5.08	14.16	19.02	24.62	2-178128-2
			X	5.08	14.16	19.02	24.62	1-178128-2
	FINISH	KEYING LOCATION	KEYING	D	C	B	A	<PART NO.>

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N. MATSUBARA CHK S.MANABE APVD S.MANABE PRODUCT SPEC APPLICATION SPEC — — WEIGHT —		01DEC93 13DEC95 13DEC95		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.2 2 PLC ± 0.25 3 PLC ± 0.3 4 PLC ± — ANGLES ± 3°		NAME DYNAMIC D-3200, 5.08 PITCH RECEPTACLE HOUSING (KEY:X,Y)		RESTRICTED TO	
		MATERIAL SEE NOTE		FINISH —		SIZE A2	
				CAGE CODE 00779		DRAWING NO C-178128	
				SCALE 1:1		SHEET 1 of 2	
				REV J			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—

本図 1- -5,2- -5,1- -6,2- -6:AS SHOWN

NOTE

1 MATERIAL:GLASS FIELD THERMO PLASTIC,POLYESTER

BLACK	EXCEPT 7-178128-3
ORANGE	7-178128-3
COLOR	PART NUMBER


- △ TO COAT ALL SURFACE OF HOUSING WITH TEFLON

3 PRODUCT SPEC. : 108-5349

4 THE SHAPE,SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE THEY DON'T SHOW DETAILS

注記

- 1 材料：ガラス入り熱可塑性ポリエステル樹脂
- | | |
|------|---------------|
| 黒 | 7-178128-3 以外 |
| オレンジ | 7-178128-3 |
| 色 | 製品番号 |
- △ ハウジング全面にテフロン塗装のこと
- 3 製品規格 : 108-5349
- 4 文字の形状、大きさ、および位置については、
大略を示すものであり、 詳細を示すものではありません。



	Y	25.4	34.48	39.34	44.94	2-178128-6
	X	25.4	34.48	39.34	44.94	1-178128-6
	Y	20.32	29.4	34.26	39.86	2-178128-5
	X	20.32	29.4	34.26	39.86	1-178128-5
						6-178128-4
						5-178128-4
						2-178128-4
						1-178128-4
						7-178128-3
						6-178128-3
						5-178128-3
						3-178128-3
						2-178128-3
						1-178128-3
						6-178128-2
						5-178128-2
						2-178128-2
						1-178128-2
キーイング 位置 KEYING LOCATION	キーイング KEYING	D	C	B	A	製品番号 (PART NO.)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
K.IKEDA
CHK
Y.ISHIKAWA
APVD
S.MANABE
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

28JUL95
31JUL95
02AUG95

TE Connectivity

DYNAMIC D-3200, 5.08 PITCH
RECEPTACLE HOUSING (KEY:X,Y)

SIZE
A2
CAGE CODE
00779
DRAWING NO
C=178128
RESTRICTED TO
-
SCALE
1:1
SHEET
2 of 2
REV
J

1471-9 (3/11)